

SERIAL PCI INTERFACE CARD



Quick Installation Guide

Introduction

RS-232 Golden I/O series, a line of Universal PCI Multi-port Serial Communication Board, is a 32-bit Plug-n-Play PCI Bus card equipped with independent high-speed RS-232.V24 standard serial interfaces. The card attaches 1 / 2 / 4 independent DB9 or DB25 RS-232 serial ports on your system for industrial communication and automation applications. It is compatible with both 3.3V or 5V and 32-bit or 64-bit PCI Bus, allowing this multi-port serial card to be installed in virtually any available PC system and compatible with all major operating systems. Users do not need to manually set jumpers to configure I/O addresses and IRQ locations. The system will search the device automatically eliminating any conflicts with other cards or devices.

Features

- Fully compatible with PCI Spec. Ver2.2 / 2.1standard.
- Supports 64-bit & 32-bit PCI Bus and 3.3V &5V connector keys.
- Expands 1 / 2 / 4 independent RS-232 serial ports in one single board.
- High speed 16C950 compatible communication controller with SUN1989 single chip hardware flow control to guarantee no data loss and best technical support.
- Each serial port has built-in 128 byte hardware FIFO.
- Data transmission speeds up to 115.2 Kbps.
- Certified by Microsoft WHQL, CE, FCC Class B approval.
- Support Microsoft Windows, DOS, Linux, and SCO Unix major operation system.
- Ready for the Intel® and AMD® 32 and 64-bit platform system.

Package List

Please check if the following items are present and in good condition upon opening your package. Contract your vendor if any item is damaged or missing.

- RS-232 Universal PCI Multi-Port Communication Board
- Quick Installation Guide (this document)
- CD Driver
- User Manual Serial Cable (Note)
- Low Profile Bracket(s) (optional)

1 port series: Do NOT need any connection cable.2 ports series: Do NOT need any connection cable.

4 ports series: DB44 Male to 4 ports DB9 or DB25 Male × 1

NOTE

We provide 1, 2 or 4 RS-232 ports product for user's selection. The expansions COM ports and cable accessory will depend on what product you bought.

RS-232 Specification

Model	RS-232 Universal PCI Communication Board
Mode of Operation	HandShaking RS-232 Full-Duplex
Controller	16C650 Compatible UART
Bus Interface	64-bit & 32-bit PCI Bus / 3.3V & 5V Connectory Key
Number of Ports	1 / 2 / 4 / 8 ports with DB9 or DB25 Male Type
Bracket	Standart 121 mm, Low Profile 79.2 mm
IRQ & IO Address	Assigned by BIOS / O.S.
FIFO	32 byte hardware FIFO
Baud Rate	75~115, 200bps
Data Bit	5, 6, 7, 8
Stop Bit	1, 1.5, 2
Parity	Even, Odd, None, Mark, Space
Flow Control	None, Xon/Xoff, HardWare
Pin Assignment	T x D, R x D, RTS, CTS, DTR, DSR, DCD, RI, GND
	2 3 4 6 6 7 8 1 2 3 4 6 1 2 3 4 6 1 2 3 4 6 1 2 3 4 6 1 2 3 4 6 1 2 3 4 6 1 2 3 4 6 1 2 3 4 6 1 2 3 4 6 1 2 3 4 6 1 2 3 4 6 1 2 3 4 6 1 2 3 6 7 8 9 1 2 3 4 5 6 7 8 9 1 2 3 4
Driver Support	Windows 2000 / 2D03 / 2008 / XP / Vista / 7
	Linux 2.2.x, 2.4.x, 2.6.x, DOS
Regulatory Approvals	CE, FCC / Microsoft WHQL
Operation Temperature	0°C ~ 60°C (32°F~140°F)

Driver Installation

In order to ensure proper operation of your RS-232 PCI serial board, the driver will be in the CD bound with your product. You can specify the location (folder) as below:

Operation System	Driver Location
Windows 2000 / 2003 / 2008 / XP /	:\RS232\PCI RS232\2K&XP&2003&Vista&7&2008
Vista / 7 (32/64 bit)	
DOS	:\RS232\PCI RS232\DOS\SUNDOS.EXE
Windows CE.NET	:\RS232\PCI RS232\WinCE
Linux 2.4.x, 2.6.x	:\RS232\PCI RS232\Linux

^{*} You can find the detail of the installation steps in the user manual.

Hardware Verity

Please launch the "Device Manager" to verity hardware installation correctly. Start > Controller Panel > System > Device Manager




* The number of COM ports will depend on what products you bought.

Port Setting

After installing RS-232 PCI serial board successfully, you can modify the setting for each serial port in device manager.

1. Right click your mouse on the COM port, and select "Properties".



- 2. Select "Port Setting" page to modify COM port setting.
- 3. Select "Advanced" icon, you can modify COM port number and FIFO.

